


RoHS




SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°c to +105°c

Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)



Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



料号 : PH-00174

Dimension antitheses list					
ITEM	PC	PB	PA	L	TYPE
Standard	3.00	10.50	3.00	16.50	Type01
Alternate					

深圳市连盛精密连接器有限公司

OPERATION		DRAW		SCALE		FIT		PART NO.	
X.X	±0.30	X.X	±0.30	UNIT	mm	1/1	A4	A0006-PH-00174	
X.XX	±0.20	CHECK		SIZE	A4	SHEET		2.54PH 2H=2X2.5 1X3P	
X.XXX	±0.10	APPROVE		PROJ.	1/1	TITLE:		PA=PC=3.0 PB=10.5 PA6T	
Angle	±3°								
DIM	TOL								
OPERATION		DRAW		SCALE		FIT		PART NO.	
DRAW		CHECK		UNIT		mm		A0006-PH-00174	
APPROVE		APPROVE		SIZE		A4		2.54PH 2H=2X2.5 1X3P	
APPROVE		APPROVE		PROJ.		1/1		PA=PC=3.0 PB=10.5 PA6T	

REV 1 DATE 2014.04.16 MODIFICATION DESCRIPTION NEW DRAWING CHANGE DIM TOL