





RoHS

SPECIFICATIONS

Rated Current:1.5AMP  
 Contact Resistance:20mΩ Max  
 Withstand Voltage:500V AC/DC  
 Insulation Resistance:1000MΩ Min  
 Operation Temperature:-40°C to +105°C

Contact Material:Brass  
 Contact Plating:Au Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PA6T  
 Max.Processing Temp: 230°C for 30-60 seconds  
 (260°C for 5 seconds)

Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list			
ITEM	PC	PA	L
Alternate	2.35	2.35	8.70

				OPERATION		DRAW		SCALE		FIT		深圳市连盛精密连接器有限公司	
				X.X	±0.30			UNIT	mm				
				X.XX	±0.20	CHECK		SIZE	A4	PART NO.		PH-00261	
A0	2012.04.11	NEW DRAWING		X.XXX	±0.10	APPROVE		SHEET	1/1	TITLE:		2.0PH 2x3pin 2H=2X2.0mm PA=PC=2.35 L=8.7	
REV	DATE	MODIFICATION DESCRIPTION		CHANGE	DIM	TOL			PROJ.				
1	2	3	4	5	6	7	8	9					