




# RoHS

## SPECIFICATIONS

Rated Current:3.0AMP  
 Contact Resistance:20mΩ Max  
 Withstand Voltage:1000V AC/DC  
 Insulation Resistance:1000MΩ Min  
 Operation Temperature:-40°c to +105°c

Contact Material:Brass  
 Contact Plating:Au Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PA6T  
 Max.Processing Temp: 230°C for 30-60 seconds  
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list						
ITEM	PC	PB	PA	L	TYPE	
Standard	3.00	13.32	3.00	19.32		
Alternate						

深圳市连盛精密连接器有限公司

OPERATION		DRAW		SCALE		FIT		PART NO.	
X.X	±0.30	X.X	±0.30	UNIT	mm	UNIT	mm	SIZE	A4
X.XX	±0.20	CHECK		SHEET		1/1		TITLE:	
X.XXX	±0.10	APPROVE		PROJ.		◆		2.54PH 1X20P PA=FC=3.0	
Angle	±3°	TOL		DIM		TOL		PB=13.32 PA6T	
A0	2014.04.16	NEW DRAWING		CHANGE		CHANGE		PH-00409---A0001	
REV	DATE	MODIFICATION DESCRIPTION		CHANGE		CHANGE		TITLE:	
1								PH-00409---A0001	