




Recommended P.C.B Layout(Top Side)  
(PCB BOARD TOLERANCE±0.05)



**SPECIFICATIONS**  
 Rated Current:3.0AMP  
 Contact Resistance:20mΩ Max  
 Withstand Voltage:1000V AC/DC  
 Insulation Resistance:1000MΩ Min  
 Operation Temperature:−40°c to +105°c  
 Contact Material:Brass  
 Contact Plating:Au Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PA6T  
 Max.Processing Temp: 230°C for 30–60 seconds  
 (260°C for 10 seconds)



注:中间塑胶居中

301100203D2SSR002

Dimension antitheses list				
ITEM	PA	PC	PB	L
Alternate	6.00	3.00	38.00	47.00

深圳市连盛精密连接器有限公司

OPERATION		DRAW		SCALE		FIT		PART NO.	
X.X	±0.30	X.X	±0.30	UNIT	mm	SIZE	A4	A0001-PH-00482	
X.XX	±0.20	CHECK		SHEET		1/1		TITLE:	
X.XXX	±0.10	APPROVE		PROJ.		◆		2.54PH 3H=3X2.5 DIP PA6.0 PB36.0 PC3.0 PA6T	
Angle	±3°	DIM		TOL		7		8	
REV	DATE	MODIFICATION DESCRIPTION		CHANGE		4		5	
A0	2012.08.03	NEW DRAWING							
1									