





RoHS

SPECIFICATIONS

Rated Current: 1.5AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 500V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°C to +105°C
 Contact Material: Brass
 Contact Plating: Au Over Ni
 Insulator Material: Polyester (UL94V-0)
 Standard: PA6T
 Max. Processing Temp: 230°C for 30-60 seconds
 (260°C for 5 seconds)



Recommended P.C.B Layout (Top Side)
 (PCB BOARD TOLERANCE ±0.05)



Dimension antitheses list			
ITEM	PC	PA	L
Standard	2.80	4.10	8.90
Alternate			

深圳市连盛精密连接器有限公司

OPERATION		DRAW		SCALE		FIT		PART NO.	
X.X	±0.30			UNIT	mm				
X.XX	±0.20	CHECK		SIZE	A4			PH-00848	
X.XXX	±0.10			SHEET	1/1			TITLE: 2.0PH H=2.0 2X8P DIP PA4.1 PC2.8	
Angle	±3°	APPROVE		PROJ.				L=8.9 AU PA6T	
DIM	TOL								

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
A0	2018.08.29	NEW DRAWING	
1			