



# RoHS

## SPECIFICATIONS

Rated Current:3.0AMP  
 Contact Resistance:20mΩ Max  
 Withstand Voltage:1000V AC/DC  
 Insulation Resistance:1000MΩ Min  
 Operation Temperature:-40°C to +105°C

Contact Material:Brass  
 Contact Plating:Tin Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PA6T  
 Max.Processing Temp: 230°C for 30-60 seconds  
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list			
ITEM	PA	PC	L
Standard	6.00	3.00	11.50
Alternate			

深圳市连盛精密连接器有限公司

				OPERATION		DRAW		SCALE	FIT	PART NO. PH-01078	
				X.X	±0.30			UNIT	mm		
				X.XX	±0.20	CHECK		SIZE	A4	TITLE: 2.54PH H=2.5 1X2P DIP PA6.0 PC3.0 L=11.5 PA6T	
				X.XXX	±0.10			SHEET	1/1		
A0	2012.03.28	NEW DRAWING		Angle	±3°	APPROVE		PROJ.			
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL						