





RoHS

SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact Plating:Tin Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list			
ITEM	PA	PC	L
Standard	6.00	3.00	11.50
Alternate			

深圳市连盛精密连接器有限公司

				OPERATION		DRAW		SCALE	FIT	PART NO.	
				X.X	±0.30			UNIT	mm		
				X.XX	±0.20	CHECK		SIZE	A4	PH-01291	
				X.XXX	±0.10			SHEET	1/1		
A0	2012.03.28	NEW DRAWING		Angle	±3°	APPROVE		PROJ.		TITLE: 2.54PH H2.5mm 2x3P 180°	
REV	DATE	MODIFICATION DESCRIPTION		DIM	TOL						