



RoHS

SPECIFICATIONS



Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°c to +105°c

Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



空第5-6P



				OPERATION		DRAW	SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30		UNIT	mm		
				CHECK		APPROVE	SIZE	A4	PART NO. PH-01337	
				X.XX	±0.20		SHEET	1/1	TITLE: 2.54PH 2H=2x2.5 2X4P 空第5-6P DIP PA3.0 PB17.0 PC3.0 L=23.0 PA6T	
A0	2012.03.28	NEW DRAWING		Angle	±3°	PROJ.				
REV	DATE	MODIFICATION DESCRIPTION		DIM	TOL					