



RoHS

SPECIFICATIONS



Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°c to +105°c

Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



空第11-12P



				OPERATION		DRAW		SCALE	FIT	深圳市连盛精密连接器有限公司	
				X.X	±0.30			UNIT	mm		
				X.XX	±0.20	CHECK		SIZE	A4	PART NO.	
				X.XXX	±0.10			SHEET	1/1	PH-01339	
A0	2012.03.28	NEW DRAWING		Angle	±3°	APPROVE		PROJ.		TITLE:	
REV	DATE	MODIFICATION DESCRIPTION		DIM	TOL					2.54PH 2H=2x2.5 2X8P 空P DIP PA=PC=3.0 PB17.0 L=23.0 PA6T	