





RoHS

SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact Plating:Au Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 10 seconds)

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list			
ITEM	PA	PC	L
Standard	9.00	3.00	14.50
Alternate			

		OPERATION		DRAW		SCALE	FIT	深圳市连盛精密连接器有限公司	
		X.X	±0.30			UNIT	mm		
				CHECK		SIZE	A4	PART NO. 16F1002000447	
		X.XX	±0.20			SHEET	1/1		
A0	2012.03.28	NEW DRAWING				APPROVE		TITLE: 2.54PH H2.5mm 2x10P 180°	
REV	DATE	MODIFICATION DESCRIPTION		CHANGE		DIM	TOL		