


# ROHS




## SPECIFICATIONS

Rated Current: 3.0AMP  
 Contact Resistance: 20mΩ Max  
 Withstand Voltage: 1000V AC/DC  
 Insulation Resistance: 1000MΩ Min  
 Operation Temperature: -40°c to +105°c

Contact Material: Brass  
 Contact Plating: Au Over Ni  
 Insulator Material: Polyester(UL94V-0)  
 Standard: PA6T  
 Max. Processing Temp: 230°C for 30-60 seconds  
 (260°C for 10 seconds)



Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE±0.05)



Dimension antitheses list					
ITEM	PC	PB	PA	L	TYPE
Standard	3.30	6.60	5.70	15.6.0	Type01
Alternate					

深圳市连盛精密连接器有限公司

PART NO. PH-01517

TITLE: 2.54PH 2H=2X2.5 1X40P DIP PA5.7  
 PB6.6 PC3.3 L=15.6 AU0.6U PA6T

OPERATION		DRAW		SCALE		FIT	
X.X	±0.30	X.XX	±0.20	UNIT	mm	SIZE	A4
X.XXX	±0.10	CHECK		SIZE	A4	SHEET	1/1
Angle	±3°	APPROVE		PROJ.	1/1		
DIM	TOL						

REV	DATE	MODIFICATION DESCRIPTION	CHANGE
A0	2014.04.16	NEW DRAWING	

1	2	3	4	5	6	7	8	9
---	---	---	---	---	---	---	---	---