

SPECIFICATION FOR APPROVAL

CUSTOMER		CUST P/N.	
ITEM	Radial Choke Inductor	Description	RL0608N-2R2M
PART NO.	303-79566	DATE	2019.08.13

<p>(1) DIMENSION(UNIT:mm)</p>		A	9.0 (Max)	mm
		B	11.0 (Max)	mm
		C	3.5± 0.5	mm
		D	3.0±1.0	mm
		E	∅0.65 ± 0.1	mm
		F		mm
		G		mm
		H		mm

(2)ELECTRICAL REQUIREMENTS			
TEST CONDITION	FREQUENCY	VOLTAGE	(3) TEST INSTRUMENTS
			LCR-METER:
L	2.2μH±20%	200KHz 0.25V	V
			HP-4291A WK3260B
DCR	25.0mΩ(Max)	KHz V	V
			DC RESISTANCE METER: WK3260B
IDC	6.0A (Max)	200KHz 0.25V	V
			CURRENT SOURCE: WK3260B
		KHz V	RFIMPEDANCE/MATERIAL ANALYZER
			HP-4291A
		MHz V	GW PUNCTURE INSULATION TESTER

(4)TURN: 8Ts(REF)

(5)MATERIAL LIST		
ITEM	MATERIAL	DESCRIPTION
1	CORE	SR60 DR6×8 ^{D-31}
2	WIRE	∅0.5mm(2UEW)
3	TUBE	UL ∅6×10mm
4		

REMARK:	APPROVED	CHECKED	DRAWN BY
	姜杰文	姜法寶	王艷