



CUT-OUT



**MATERIAL:**

Cover:Nylon66,UL rated:94V-2 min  
 Base:Nylon66,UL rated:94V-2 min  
 Terminal:Brass,Silver plating

Rating: 0.2A 250VAC \0.5A 12VDC  
 Nut Torque:5~14Nm  
 Contact Resistance: 50mΩ MAX.  
 Insulation Resistance: 100MΩ min.at 500VDC  
 Dielectric Strength: 1500 VAC 1 minute.  
 Electrical life: 50,000 cycles  
 Mechanical life :100,000 cycles  
 Operating Temperature: -20°C~80°C  
 Operating Pressure:3.5±1.0N  
 Operating Stroke:2.5±1.0mm  
 Protection Grade:IP65  
 Soldering:300°C max.for 5 seconds  
 Function:(ON)-OFF  
 Lamp Type:LED  
 Lamp Life:50000H  
 Lamp current : 20mA Max



|                |                         |         |         |               |  |     |  |                  |  |              |  |                       |  |
|----------------|-------------------------|---------|---------|---------------|--|-----|--|------------------|--|--------------|--|-----------------------|--|
|                |                         |         |         | 公差 TOLERANCES |  |     |  | .X± 0.5 .XX± 0.3 |  | 角度 ANGLE ±1° |  | 单位 DIMENSION UNIT mm. |  |
| 版本 VERSION     |                         | A0      |         | 比例尺 SCALE     |  | 1:1 |  | 日期 DATE          |  | 2021.06.08   |  | 品名 TITLE              |  |
| 核准 APPROVED BY |                         |         |         | 核对 CHECKED BY |  |     |  | 绘图 DRAWN BY      |  | 孙成           |  | PB-12M12-SPRR-FB      |  |
| 版本 VER.        | 变更说明 CHANGE DESCRIPTION | 日期 DATE | ECN NO. |               |  |     |  |                  |  |              |  | 图号 DRAWING NO         |  |
|                |                         |         |         |               |  |     |  |                  |  |              |  | PB-12M12-SPRR-FB_A0   |  |