



Nut Torque: 5 ~ 14Nm
 Protection Grade: IP67, IK08
 Shell: SUS
 Base: PBT
 Lamp Type: LED
 Lamp current : 20mA Max
 Lamp Life: 50000H
 Beads Color: Green
 Lamp voltage: 24V
 Operating Temperature: -20°C~80°C
 Safety Approval: RoHS

公差 TOLERANCES .X±0.5 .XX±0.3 角度 ANGLE ±1° 单位 DIMENSION UNIT mm.



版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	核准 APPROVED BY	核对 CHECKED BY	绘图 DRAWN BY	品名 TITLE	图号 DRAWING NO
				版本 VERSION	比例尺 SCALE	日期 DATE	PBM-19111-FS-G1-A24-S7S-A3	PBM-19111-FS-G1-A24-S7S-A3_A0
				A0	1:1	2020.06.08		
				核准	核对	孙成		