



CUT-OUT

Nut Torque: 5 ~ 14Nm
 Protection Grade: IP65, IK08
 Shell: Brass, Ni Plating
 Button: PC
 Base: PBT
 Lamp Type: LED
 Forward current : 20mA
 Lamp Life: 50000H
 Operating Temperature: -20°C~80°C
 Safety Approval: **RoHS**



公差 TOLERANCES .X± 0.5 .XX± 0.3 角度 ANGLE ±1° 单位 DIMENSION UNIT mm.

版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	核准 APPROVED BY	核对 CHECKED BY	绘图 DRAWN BY	品名 TITLE	图号 DRAWING NO
				A0		孙成	PBM-22113-FS-RG3-A24-B8S-A3	PBM-22113-FS-RG3-A24-B8S-A3_A0