


**CUT-OUT**

Nut Torque:5 ~ 14Nm  
 Protection Grade:IP67,IK08  
 Shell:Brass,Ni Plating  
 Base:PA66  
 Lamp Type:LED  
 Forward current : 20mA MAX  
 Lamp Life:50000H  
 Beads Color:Green  
 Lamp voltage:220V AC  
 Operating Temperature:-20°C~80°C  
 Relative Air Humidity:45%~85%  
 Safety Approval:



					 <b>D-SWITCH</b> <sup>®</sup> 东莞市德崧电子有限公司 D-SWITCH ELECTRONICS CO.,LTD					
		公差 TOLEANCES		.X± 0.5	.XX± 0.3	角度 ANGLE ±1°		单位	DIMENSION UNIT	mm.
		版本 VERSION	A0	比例尺 SCALE	1:1	日期 DATE	2021.06.08	品名 TITLE	图号	DRAWING NO
		核准		核对		绘图	孙成	PBM-8I11-FS-G1-S220-B8S	PBM-8I11-FS-G1-S220-B8S_A0	
版本 VER.	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	APPROVED BY	CHECKED BY	DRAWN BY				