





环保物料

TEL:0769-82001899



SPECIFICATION

- *Current Rating :1A
- *Insulator Resistance :1000 MΩ Min.
- *Contact Resistance :20 mΩ Max.
- *Dielectric With Standing:AC 500V
- *Operating Temperature :-40℃ To +105℃
- *Contact Material :C5191
- *Insulator Material :Polyester, UL94V-0
- * Standard :PA9T
- *Finish :Gold Flash All Over Nickel



Recommended P.C.B Layout

PIN NO.	DIMENSION	
	A	B
2*2	1.27	3.04
2*3	2.54	4.31
2*4	3.81	5.58
2*5	5.08	6.85
2*6	6.35	8.12
2*7	7.62	9.39
2*8	8.89	10.66
⋮	⋮	⋮
2*50	62.23	64.0

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN 兴飞连接器有限公司 XFCN CONNECTORS CO.,LTD.		SHEET	1/1
				X.	±0.30	X°	±5°			CHKD	
				.X	±0.20	.X°	±2°	APPD		UNITS	mm
				.XX	±0.08	.XX°	±1°			SCALE	1:1
AO				.XXX	±0.03	.XXX°	±0.5°	VIEW	⊕	PRODUCT NAME	1.27mm Female Header Connectors
VER	MODIFICATION	DRAW	DATE							PART. NO.	PM127VS-12-xx-H34-4.5-R
1	2	3	4	5	6	7	8	9	10	DWG. NO.	009