





# Kinghelm®

编号	修改原因	制图	审核	核准


PROD.NO.			A(mm)	B(mm)
KF1027-A-02	KF1027-B-02	KF1027-C-02	6.08	2.54
KF1027-A-03	KF1027-B-03	KF1027-C-03	8.62	5.08
KF1027-A-04	KF1027-B-04	KF1027-C-04	11.16	7.62
KF1027-A-05	KF1027-B-05	KF1027-C-05	13.70	10.16
KF1027-A-06	KF1027-B-06	KF1027-C-06	16.24	12.70
KF1027-A-07	KF1027-B-07	KF1027-C-07	18.78	15.24
KF1027-A-08	KF1027-B-08	KF1027-C-08	21.32	17.78
KF1027-A-09	KF1027-B-09	KF1027-C-09	23.86	20.32
KF1027-A-10	KF1027-B-10	KF1027-C-10	26.40	22.86
KF1027-A-11	KF1027-B-11	KF1027-C-11	28.94	25.40
KF1027-A-12	KF1027-B-12	KF1027-C-12	31.48	27.94



**KF1027-A**



**KF1027-B**



**KF1027-C**

<b>尺寸公差:</b>		<b>角度公差:</b>		<b>投影法</b>		<b>品名</b>	<b>开关</b>
X.	±0.25	X.	±5°	<b>单位</b>	mm	间距2.54MM	
.X	±0.15	.X	±3°	<b>纸张尺寸</b>	A4	<b>产品系列</b>	KF1027 系列
.XX	±0.10	.XX	±2°	深圳市金航标电子有限公司			WWW.BDS666.COM
<b>图纸类型</b>	CUSTOMER			KH-10027A-HL2.54-4P			0755-83044319
<b>比例</b>	1:1	<b>图页</b>	1\1				
<b>图纸编号</b>	KF1027						