





Kinghelm®

编号	修改原因	制图	审核	核准


PROD.NO.			A(mm)	B(mm)
KF1027-A-02	KF1027-B-02	KF1027-C-02	6.08	2.54
KF1027-A-03	KF1027-B-03	KF1027-C-03	8.62	5.08
KF1027-A-04	KF1027-B-04	KF1027-C-04	11.16	7.62
KF1027-A-05	KF1027-B-05	KF1027-C-05	13.70	10.16
KF1027-A-06	KF1027-B-06	KF1027-C-06	16.24	12.70
KF1027-A-07	KF1027-B-07	KF1027-C-07	18.78	15.24
KF1027-A-08	KF1027-B-08	KF1027-C-08	21.32	17.78
KF1027-A-09	KF1027-B-09	KF1027-C-09	23.86	20.32
KF1027-A-10	KF1027-B-10	KF1027-C-10	26.14	22.86
KF1027-A-11	KF1027-B-11	KF1027-C-11	28.94	25.40
KF1027-A-12	KF1027-B-12	KF1027-C-12	31.48	27.94



KF1027-A



KF1027-B



KF1027-C

尺寸公差:		角度公差:		投影法		品名	开关
X.	±0.25	X.	±5°	单位	mm	间距2.54MM	
.X	±0.15	.X	±3°	纸张尺寸	A4	产品系列	KF1027 系列
.XX	±0.10	.XX	±2°	深圳市金航标电子有限公司			WWW.BDS666.COM
图纸类型	CUSTOMER			KH-10027B-SMT2.54-2P			0755-83044319
比例	1:1	图页	1\1				
图纸编号	KF1027						