



Specifications:

规格:

1.Voltage rating:250VAC/DC

额定电压: 250V AC/DC

2.Current rating:1A AC/DC

额定电流: 1A AC/DC

3.Withstanding voltage:500V AC/minute

耐受电压: ≥500V AC/分钟

4.Temperature range:-40℃-+105℃

温度范围: -40℃-+105℃

5.Insulation resistance:1000MΩMIN

绝缘电阻: ≥1000MΩ

6.Contact resistance:20mΩMax

接触电阻: ≥20mΩ

Material:

材料:

7.Rubber core:PBT UL94V-0

胶芯: PBT UL94V-0

8.The iron shell:SPCC Nivkel Plating/Tin Plating

铁壳: SPCC, 镀镍/镀锡

B、成品不能有弯针，R角不一致等不良。

X07 XX F X X X 1

① ② ③ ④ ⑤ ⑥ ⑦

① Series NO.

② Row No.Pin No.XX-09;15;25;37

③ Welding Board Angle :F-Female

④ T: Tradtional C: Car-pin

⑤ Planting Category: 1:1U 2:2U 3:3U 4:4U 5:5U 6:6U 7:AuSn

⑥ Color:B-BLACK W-White BL-Blue

⑦ 1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4; 5:TYPE-5

NUMBER OF POSITIONS	DIMENSION				
	A±0.40	B±0.30	C±0.30	D±0.25	E±0.25
9	30.80	25.00	16.35	11.08	10.16
15	39.14	33.30	24.75	19.39	17.78
25	53.05	47.04	38.35	33.24	30.38
37	69.32	63.50	54.75	49.86	45.72

X07XXFXXX1	XDBLS	XDBLM
PART NO	SCREW	NUT

					ANGLAR	±5°	DSND		SCALE: N/A	MODEL TYPE: D-USB		
Δx					L ≤ 4	±0.2	DWN		VIEW:	PART NO.: X07XXFXXX1		
Δx					4 < L ≤ 16	±0.3	CHKD		UNIT: mm/in	DWG NO.: X-X07XXFXXX1		
Δx					16 < L ≤ 63	±0.4	APPD		SIZE: A4			
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5				WEIGHT	SHEET	REVISION
REVISIONS					UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO., LIMITED			1/1	A0	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn												