




**X08 XX F X X X 3**  
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series NO.
- ② Row No.Pin No.XX-09;15;25;37
- ③ Welding Board Angle :F-Female
- ④ T: Tradutional C: Car-pin
- ⑤ Planting Category: 1:1U 2:2U 3:3U 4:4U 5:5U 6:6U 7:7AuSn
- ⑥ Color:B-BLACK W-White BL-Blue
- ⑦ 1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4; 5:TYPE-5

NUMBER OF POSITIONS	DIMENSION				
	A±0.40	B±0.30	C±0.30	D±0.25	E±0.25
9	30.80	25.00	16.35	11.08	10.16
15	39.14	33.30	24.75	19.39	17.78
25	53.05	47.04	38.35	33.24	30.38
37	69.32	63.50	54.75	49.86	45.72



X08XXFXXX3	XDBLS	XDBLM
PART NO	SCREW	NUT



DSND	SCALE: N/A	MODEL TYPE: D-USB
DWN	VIEW:	PART NO.: X08XXFXXXX
CHKD	UNIT: mm/in	DWG NO.: X-X08XXFXXXX
APPD	SIZE: A4	WEIGHT SHEET REVISION 1/1 A0

MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
					L > 63	±0.5
REVISIONS						UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



XKB INDUSTRIAL PRECISION CO.,LIMITED

Specifications:

- 规格:
- Voltage rating:250VAC/DC  
额定电压: 250V AC/DC
  - Current rating:1A AC/DC  
额定电流: 1A AC/DC
  - Withstanding voltage:500V AC/minute  
耐受电压: ≥500V AC/分钟
  - Temperature range:-40℃-+105℃  
温度范围: -40℃-+105℃
  - Insulation resistance:1000MΩMIN  
绝缘电阻: ≥1000MΩ
  - Contact resistance:20mΩMax  
接触电阻: ≥20mΩ

Material:

- 材料:
- Rubber core:PBT UL94V-0  
胶芯: PBT UL94V-0
  - The iron shell:SPCC Nivkel Plating/Tin Plating  
铁壳: SPCC,镀镍/镀锡
- B、成品不能有弯针，R角不一致等不良。