

Specifications:

规格:

- 1.Voltage rating:250VAC/DC  
额定电压: 250V AC/DC
- 2.Current rating:1A AC/DC  
额定电流: 1A AC/DC
- 3.Withstanding voltage:500V AC/minute  
耐受电压: ≥500V AC/分钟
- 4.Temperature range:-40℃~+105℃  
温度范围: -40℃~+105℃
- 5.Insulation resistance:1000MΩMIN  
绝缘电阻: ≥1000MΩ
- 6.Contact resistance:20mΩMax  
接触电阻: ≥20mΩ

Material:





材料:

- 7.Rubber core:PBT UL94V-0  
胶芯: PBT UL94V-0
  - 8.The iron shell:SPCC Nivkel Plating/Tin Plating  
铁壳: SPCC,镀镍/镀锡
- B、成品不能有弯针，R角不一致等不良。

X08 XX F X X X 1

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series NO.
- ② Row No.Pin No.XX-09;15;25;37
- ③ Welding Board Angle :F-Female
- ④ T: Tradutional C: Car-pin
- ⑤ Planting Categotry: 1:1U 2:2U 3:3U 4:4U 5:5U 6:6U 7:7AuSN
- ⑥ Color:B-BLACK W-White BL-Blue
- ⑦ 1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4; 5:TYPE-5



| NUMBER OF POSITIONS | DIMENSION |        |        |        |        |
|---------------------|-----------|--------|--------|--------|--------|
|                     | A±0.40    | B±0.30 | C±0.30 | D±0.25 | E±0.25 |
| 9                   | 30.80     | 25.00  | 16.35  | 11.08  | 10.16  |
| 15                  | 39.14     | 33.30  | 24.75  | 19.39  | 17.78  |
| 25                  | 53.05     | 47.04  | 38.35  | 33.24  | 30.38  |
| 37                  | 69.32     | 63.50  | 54.75  | 49.86  | 45.72  |

|            |       |       |
|------------|-------|-------|
| X08XXFXXX1 | XDBLS | XDBLM |
| PART NO    | SCREW | NUT   |

|   |             |      |         |          |             |                                      |  |            |                          |       |          |
|---|-------------|------|---------|----------|-------------|--------------------------------------|--|------------|--------------------------|-------|----------|
|   |             |      |         |          |             | DSND                                 |  | SCALE: N/A | MODEL TYPE:<br>D-USB     |       |          |
| ΔX  |             |      |         |          | ANGLAR      |                                      |  | VIEW:      | PART NO.:<br>X08XXFXXX1  |       |          |
| ΔX  |             |      |         |          | L ≤ 4       | ±0.2                                 |  |            | DWG NO.:<br>X-X08XXFXXX1 |       |          |
| ΔX  |             |      |         |          | 4 < L ≤ 16  | ±0.3                                 |  |            |                          |       |          |
| MARK  | DESCRIPTION | DATE | REVISED | APPROVED | 16 < L ≤ 63 | ±0.4                                 |  |            |                          |       |          |
|   | REVISIONS   |      |         |          | L > 63      | ±0.5                                 |  |            |                          |       |          |
|   |             |      |         |          |             | UNSPECIFIED TOLERANCES               |  |            | WEIGHT                   | SHEET | REVISION |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn |             |      |         |          |             | XKB INDUSTRIAL PRECISION CO.,LIMITED |  |            | 1/1                      | A0    |          |