

HSF RoHS **c** **RoHS** **us** **CE**

SPECIFICATIONS

Rated(额定参数): 300V,8A
 Dielectric strength(抗电强度): AC1500V/1 Minute
 Insulation Resistance(绝缘电阻):1000MΩ Min
 Contact Resistance(接触电阻):20mΩ Max
 Screw Torque(扭矩): 0.2Nm (1.7Lb.in)
 Wire Range(线径):16~28AWG
 Strip length(剥线长度):6~7mm
 Temp. range(操作温度): -40℃~+105℃
 MAX Soldering(瞬时温度):+260℃,5s

Housing Material(塑件): PA66 (UL94 V-0)
 Contact(端子): Phosphor Bronze, Tin plating(磷铜镀镍)
 Clamp(方块): Brass(黄铜), Ni plating(镀镍)
 Screw (螺丝): M2.0 Steel, Zinc plating(钢,镀锌)

PITCH RANGE IN MM			NOMINAL DIMENSION RANGE IN MM				
T0	OVER	OVER	T0	OVER	OVER	OVER	OVER
6	6	10	30	30	60	100	150
	T0	T0	T0	T0	T0	T0	T0
	10	24	30	60	100	150	150
±0.10	±0.15	±0.25	±0.30	±0.30	±0.50	±0.70	±1.00

Ordering Information






JL15EDGKA - XXX XX G X 1

Pitch
350=3.5PH
381=3.81PH

No.of pins
2P,3P,4P~24P

Housing Color
B=Black
G=Green
U=Blue
R=Red
W=White
Y=Yellow
O=Orange
E=Grey

Packing
O=Pe bag
T=Tube
A=Tray



OPERATION	DRAW	iyusheng	20.03.03	SCALE	FIT
X.X ±0.30	CHECK			UNIT	mm
X.XX ±0.20	APPROVE			SIZE	A4
X.XXX ±0.10				SHEET	1/1
Angle ±3°				PROJ.	◆
DIM TOL					

JILN® 深圳市锦凌电子有限公司
 SHENZHEN JINLING ELECTRONIC CO.,LTD
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992

A0	2020.03.03	NEW DRAWING				PART NO.	JL15EDGKA-XXXXXGX1
REV	DATE	MODIFICATION DESCRIPTION	CHANGE			TITLE:	3.5/3.81 Pitch Female Pluggable Terminal Blocks