



SPECIFICATIONS:

Current Rating: 3A AC,DC
 Voltage Rating: 250V AC,DC
 Temperature Range: -40°C ~ +105°C
 Contact Resistance: 30mΩ Max
 Insulation Resistance: 1000MΩ Min
 Withstanding Voltage: 1000V AC/minute
 Material: Nylon 66,UL94V-0 (White)

Ordering Information & Dimensions

Circuits	Dimensions(mm)			Circuits	Dimensions(mm)		
	A	B	C		A	B	C
2P	2.00	4.60	2.30	10P	18.00	20.60	14.30
3P	4.00	6.60	2.30	11P	20.00	22.60	14.30
4P	6.00	8.60	4.30	12P	22.00	24.60	14.30
5P	8.00	10.60	6.30	13P	24.00	26.60	14.30
6P	10.00	12.60	6.30	14P	26.00	28.60	14.30
7P	12.00	14.60	6.30	15P	28.00	30.60	14.30
8P	14.00	16.60	6.30	16P	30.00	32.60	14.30
9P	16.00	18.60	6.30				



CHANGJIANG CONNECTORS CO.,LTD.

Unit	Scale	Sheet
mm	4:1	1 of 1
Draw BY:	Approved :	
Tony Su	Jack Yin	

Title :
2.00mm PITCH
HOUSING

A1	Modify drawings	2016.08.08	x.xx≤0.25	ANGLE±
A0	NEW RELEASE	2009.05.10	x.xxx≤0.20	
REV	DESCRIPTION	DATE	x.xxxx≤0.15	

DRAW NO : **A2008H-XP** REV **A1**