



Specifications:

规格:
 Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
 Current rating:3A AC/DC
 额定电流: 3A AC/DC
 Withstanding voltage:1000V AC/minute
 耐受电压: 1000V AC/分钟
 Temperature range:-25℃~+85℃
 温度范围: -25℃~+85℃
 Insulation resistance:≥1000MΩ
 绝缘电阻: ≥1000MΩ
 Contact resistance:≤10mΩ
 接触电阻: ≤10mΩ
 After environmental testing:≤20mΩ
 环境测试后: ≤20兆欧





| Poles | Dimension(mm) | | | |
|-------|---------------|-------|-------|------|
| | A | B | C | D |
| 10 | 12.00 | 8.00 | 10.60 | 5.10 |
| 12 | 14.00 | 10.00 | 12.60 | 6.80 |
| 14 | 16.00 | 12.00 | 14.60 | 6.80 |
| 16 | 18.00 | 14.00 | 16.60 | 6.80 |
| 18 | 20.00 | 16.00 | 18.60 | 6.80 |
| 20 | 22.00 | 18.00 | 20.60 | 6.80 |
| 22 | 24.00 | 20.00 | 22.60 | 6.80 |
| 24 | 26.00 | 22.00 | 24.60 | 6.80 |
| 26 | 28.00 | 24.00 | 26.60 | 6.80 |
| 28 | 30.00 | 26.00 | 28.60 | 6.80 |
| 30 | 32.00 | 28.00 | 30.60 | 6.80 |
| 32 | 34.00 | 30.00 | 32.60 | 6.80 |
| 34 | 36.00 | 32.00 | 34.60 | 6.80 |
| 36 | 38.00 | 34.00 | 36.60 | 6.80 |
| 38 | 40.00 | 36.00 | 38.60 | 6.80 |
| 40 | 42.00 | 38.00 | 40.60 | 6.80 |

X2081 H-2xXX-N0

① ② ③ ④

- 1.Series No
- 2.Category:H-HSG
- 3.Row No-Pin No:2xXX-2x05P~2x20P
- 5.Material:N0-PA66 94V-0



截面 B-B

| | | | |
|----------------|-------------------|--------------------|-----------------------|
| X2081H-2xXX-N0 | Nylon 66 UL 94V-0 | X2081W | X2081T |
| PART NO | Material | Suitable XKB Wafer | Suitable XKB Terminal |

| | | | | | |
|--------------------------------------|--|------|--|-------------|--|
| DSND | | DATE | | SCALE: N/A | MODEL TYPE: Wire to board connector |
| DWN | | DATE | | VIEW: | PART NO.: |
| CHKD | | DATE | | UNIT: mm/in | 2.00mm Crimp Style Connectors |
| APPD | | DATE | | SIZE: A4 | DWG NO.: |
| XKB INDUSTRIAL PRECISION CO.,LIMITED | | | | | X2081H-2xXX-N0 |
| | | | | | WEIGHT |
| | | | | | 1.0g 1/1 A0 |

| | | | | | |
|---|-------------|------|---------|----------|------------------------|
| | | | | | units: mm |
| ΔX | | | | | tolerance: |
| ΔX | | | | | X.X ±0.2mm |
| ΔX | | | | | X.XX ±0.1mm |
| MARK | | | | | X.XXX ±0.05mm |
| | DESCRIPTION | DATE | REVISED | APPROVED | UNSPECIFIED TOLERANCES |
| | REVISIONS | | | | |
| www.xk-dg.cn www.helloxkb.com www.helloxkb.cn | | | | | |