



SPECIFICATIONS:

Current Rating: 2A AC,DC (AWG24)
 Voltage Rating: 100V AC,DC
 Temperature Range: -40°C ~ +105°C
 Contact Resistance: 20mΩ Max.
 Insulation Resistance: 500MΩ Min.
 Withstanding Voltage: 500V AC/minute
 Pin Material: Brass/Tin over Nickel
 Material: Nylon 66,UL94V-0(White)

Ordering Information & Dimensions

Circuits	Dimensions(mm)		Circuits	Dimensions(mm)	
	A	B		A	B
2P	1.50	4.50	8P	10.50	13.50
3P	3.00	6.00	9P	12.00	15.00
4P	4.50	7.50	10P	13.50	16.50
5P	6.00	9.00	11P	15.00	18.00
6P	7.50	10.50	12P	16.50	19.50
7P	9.00	12.00	13P	18.00	21.00

CJTconn CHANGJIANG CONNECTORS CO.,LTD.

Unit mm	Scale 5:1	Sheet 1 of 1	Title : 1.50mm Pitch 180° Wafer
Draw By: Dlankul Wan	Approved : Jack Yln		
General Tolerance			

A2	CHANGE THE CURRENT RATING	2019.02.26	PROJECT ⊕ ⊖
A1	CHANGE THE DRAWING	2019.01.10	
A0	NEW RELEASE	2005.05.10	
REV	DESCRIPTION	DATE	

DRAW NO : **A1501WV-XP-WH** REV A2