


Ordering Information:

A2008HB-XP - **
1 2

- 1.Part No.
- 2.Color:
(blank) - White
BK - Black



SPECIFICATIONS:

Current Rating: 3A AC,DC
 Voltage Rating: 250V AC,DC
 Temperature Range: -40°C ~ +105°C
 Contact Resistance: 30mΩ Max.
 Insulation Resistance: 1000MΩ Min.
 Withstanding Voltage: 1000V AC/minute
 Material: Nylon 66, UL94V-0(White)

Ordering Information & Dimensions

Circuits	Dimensions(mm)			Circuits	Dimensions(mm)		
	A	B	C		A	B	C
2P	2.00	4.60	7.00	10P	18.00	20.60	23.00
3P	4.00	6.60	9.00	11P	20.00	22.60	25.00
4P	6.00	8.60	11.00	12P	22.00	24.60	27.00
5P	8.00	10.60	13.00	13P	24.00	26.60	29.00
6P	10.00	12.60	15.00	14P	26.00	28.60	31.00
7P	12.00	14.60	17.00	15P	28.00	30.60	33.00
8P	14.00	16.60	19.00	16P	30.00	32.60	35.00
9P	16.00	18.60	21.00				

CJTconn CHANGJIANG CONNECTORS CO.,LTD.

Unit	Scale	Sheet
mm	3:1	1 of 1
Draw BY:	Approved :	
Tony Su	Jack Yin	

Title :
2.00mm PITCH
HOUSING
DRAW NO : **A2008HB-XP** REV **A0**

			x.xx±0.25	ANGLE±
A0	NEW RELEASE	2013.06.25	x.xxx±0.20	
REV	DESCRIPTION	DATE	x.xxxx±0.15	