



SPECIFICATIONS:

Current Rating: 3A AC,DC
 Voltage Rating: 500V AC,DC
 Temperature Range: -40°C ~ +105°C
 Contact Resistance: 20mΩ Max
 Insulation Resistance: 500MΩ Min
 Withstanding Voltage: 1000V AC/minute
 Material: Nylon66, UL94V-0 (White)

Ordering Information & Dimensions

Circuits	Dimensions(mm)			Circuits	Dimensions(mm)		
	A	B	C		A	B	C
2P	2.50	6.80	5.00	10P	22.50	26.80	20.00
3P	5.00	9.30	5.00	11P	25.00	29.30	20.00
4P	7.50	11.80	5.00	12P	27.50	31.80	22.50
5P	10.00	14.30	7.50	13P	30.00	34.30	22.50
6P	12.50	16.80	10.00	14P	32.50	36.80	25.00
7P	15.00	19.30	12.50	15P	35.00	39.30	27.50
8P	17.50	21.80	15.00	16P	37.50	41.80	30.00
9P	20.00	24.30	17.50				



CJTconn CHANGJIANG CONNECTORS CO.,LTD.

Unit: mm, Scale: 4:1, Sheet: 1 of 1

Draw BY: Jack Yin, Approved: GONGYB

General Tolerance

Angles: x.xx±0.25, x.xx±0.20, x.xxx±0.15, ANGLE±, and a symbol for a hole with a chamfered edge.

Title: 2.50mm PITCH Housing
 DRAW NO: A2512H-XP, REV A0

REV	DESCRIPTION	DATE
A0	NEW RELEEASE	2005.07.01