



电路图

H代表; 总高

H=4.2mm

H=4.3mm

H=5.0mm ✓

H=5.5mm

H=6.0mm

H=7.0mm

H=8.0mm

H=9.0mm

H=9.5mm

H=10.0mm

H=10.5mm

Operating force	
100gf±40gf	
130gf±40gf	
160gf±40gf	
260gf±50gf	✓
350gf±50gf	

PCB LAYOUT
TOP VIEW

NO.	PART NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED		A2	2021.10.30	增加柄颜色	WM
					UP TO 5mm: ±0.1	ANGULAR ±1°				
5	SHRAPNEL	SUS	1	Ag-Plating	ABOVE 5mm: ±0.2		A1	2021.9.28	更新图纸	WM
4	TERMINAL	BRASS	4	Ag-Plated			NO	DATE	REVISIONS	BY APPD
3	COVER	SUS/BRASS	1	Ni-Plated	TITLE: TACT SWITCH			UNIT : MM	ROHS COMPLIANT	DWN
2	KNOB	PA6T	1	BLACK/RED	MODEL: TC-06104-050E			SCALE: 1:1		CHK'D
1	BASE	PA6T	1		HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司					APPD