	HAOYU								CIRCUIT DIAGRAM 1-0-2			
				0.8±0.1 0.8±0.1 0.8±0.1 0.10 0.1			5. 4. 3. 2 1 1 1 1.5 2. 7 7 0 P		Operati 100gf±40gf 160gf±40gf 260gf±50gf	ng force		
<u>8</u> 7				TOLERANCE UNLESS SPECIFIED								
6				UP TO 5mm: ±0.1 ANGULAR	1							
5 CONTACT	SUS	2	Ag-Clad	ABOVE 5mm: ±0.2 ±1°	NO	DATE		REVISIO		BY	APPD	
4CONTACT FOOT3COAT	PHOSPHOR BRONZE	1	Ag-Plating Ni-Plating	TITLE: TACT SWITCH		UNI	<u>Г: ММ</u>	ROHS	DWN			
3 COAT 2 BUTTON	PHOSPHOR BRONZE LCP	1		MODEL: TS-1114C-C SCALE: 1:1 COMPLIANT CHK'D								
1 HOUSING	LCP	1		HAOYU(HONGKONG)LIMITED								
NO. PART NAME	MATERIAL	QTY	FINISHING	B HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司					PRO.AGL:	\Rightarrow	REV :A0	
			·	·								