




电路图

Operatir	ng	force
100gf±40gf	Å	
130gf±40gf	В	
160gf±40gf	C	
200gf±50gf	D	
250gf±50gf	F	







Travel:0.2 \pm 0.1mm

PCB板焊盘尺寸

					TOLERANCE UNLESS SPECIFIED									
					UP TO 5mm: ±0.1	ANGULAR	1	2021.5.20	更新	图纸			WM	
5	STEM	LCP	1	WHITE	ABOVE 5mm: ±0.2	±1°	NO	DATE		REVISIO	NS		BY	APPD
4	COVER	BRASS	1		TITLE: TACT SV	VITCH		UNI	T : MM	ROHS	DWN	_		
3	CONTACT	SUS	1	AG-PLATED	MODEL: TS-118	8U-C				COMPLIANT	CHK'D			
_ 2	CASE	LCP	1	WHITE			ONC	KONG)LI			APPD			
1	TERMINAL	PHOSPHOR BRONZE	2	AG-PLATED								\overline{A}		
NO.	PART NAME	MATERIAL	QTY	FINISHING		皓 宇(香) 液) 有 限	公司		PRO.AC	GL: 🕀	⊕	REV :A1