



Circuits	Dimensions (mm)		
	A	B	C
PH1257-LT-02	1.25	3.85	5.80
PH1257-LT-03	2.50	5.10	7.05
PH1257-LT-04	3.75	6.35	8.30
PH1257-LT-05	5.00	7.60	9.55
PH1257-LT-06	6.25	8.85	10.80
PH1257-LT-07	7.50	10.10	12.05
PH1257-LT-08	8.75	11.35	13.30
PH1257-LT-09	10.00	12.60	14.55
PH1257-LT-10	11.25	13.85	15.80
PH1257-LT-11	12.50	15.10	17.05
PH1257-LT-12	13.75	16.35	18.30
PH1257-LT-13	15.00	17.60	19.55
PH1257-LT-14	16.25	18.85	20.80
PH1257-LT-15	17.50	20.10	22.05
PH1257-LT-16	18.75	21.35	23.30
PH1257-LT-17	20.00	22.60	24.55
PH1257-LT-18	21.25	23.85	25.80
PH1257-LT-19	22.50	25.10	27.05
PH1257-LT-20	23.75	26.35	28.30

					TOLERANCE UNLESS SPECIFIED									
					UP TO 5mm: ±0.1	ANGLES								
					ABOVE 5mm: ±0.2	±1.5°	NO	DATE	REVISIONS		BY	APPD		
4	COVER	LCP	1		TITLE: CONNECTOR			UNIT : MM	ROHS	DWN				
3	CONTACT FOOT	PBS	XX	SN-PLATED	PART NO.: PH1257-LT-XX			SCALE: 2:1	COMPLIANT	CHK'D				
2	CONTACT	PBS	2	SN-PLATED	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司							APPD		
1	HOUSING	LCP	1									PRO.AGL:	REV :A0	
NO.	PART NAME	MATERIAL	QTY	FINISHING										