



Circuits	Dimensions (mm)		
	A	B	C
PH1257-WT-02	1.25	3.85	5.80
PH1257-WT-03	2.50	5.10	7.05
PH1257-WT-04	3.75	6.35	8.30
PH1257-WT-05	5.00	7.60	9.55
PH1257-WT-06	6.25	8.85	10.80
PH1257-WT-07	7.50	10.10	12.05
PH1257-WT-08	8.75	11.35	13.30
PH1257-WT-09	10.00	12.60	14.55
PH1257-WT-10	11.25	13.85	15.80
PH1257-WT-11	12.50	15.10	17.05
PH1257-WT-12	13.75	16.35	18.30
PH1257-WT-13	15.00	17.60	19.55
PH1257-WT-14	16.25	18.85	20.80
PH1257-WT-15	17.50	20.10	22.05
PH1257-WT-16	18.75	21.35	23.30
PH1257-WT-17	20.00	22.60	24.55
PH1257-WT-18	21.25	23.85	25.80
PH1257-WT-19	22.50	25.10	27.05
PH1257-WT-20	23.75	26.35	28.30

					TOLERANCE UNLESS SPECIFIED							
					UP TO 5mm: ±0.1	ANGLES						
					ABOVE 5mm: ±0.2	±1.5°	NO	DATE	REVISIONS		BY	APPD
					TITLE: CONNECTOR			UNIT : MM	ROHS	DWN		
					PART NO.: PH1257-WT-xx			SCALE: 2:1	COMPLIANT	CHK'D		
					HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司			APPD				
								PRO.AGL:		REV :A0		
NO.	PART	NAME	MATERIAL	QTY	FINISHING							
3	CONTACT FOOT		PBS	XX	SN-PLATED							
2	CONTACT		PBS	2	SN-PLATED							
1	HOUSING		LCP	1								