



印制线路板

Circuits	Dimensions (mm)			Circuits	Dimensions (mm)		
	A	B	C		A	B	C
PH2001-LT-02	2.0	7.90	4.85	PH2001-LT-12	22.0	27.9	24.85
PH2001-LT-03	4.0	9.90	6.85	PH2001-LT-13	24.0	29.9	26.85
PH2001-LT-04	6.0	11.90	8.85	PH2001-LT-14	26.0	31.9	28.85
PH2001-LT-05	8.0	13.90	10.85	PH2001-LT-15	28.0	33.9	30.85
PH2001-LT-06	10.0	15.90	12.85	PH2001-LT-16	30.0	35.9	32.85
PH2001-LT-07	12.0	17.90	14.85	PH2001-LT-17	32.0	37.9	34.85
PH2001-LT-08	14.0	19.90	16.85	PH2001-LT-18	34.0	39.9	36.85
PH2001-LT-09	16.0	21.90	18.85	PH2001-LT-19	36.0	41.9	38.85
PH2001-LT-10	18.0	23.90	20.85	PH2001-LT-20	38.0	43.9	40.85
PH2001-LT-11	20.0	25.90	22.85				

					TOLERANCE UNLESS SPECIFIED							
					UP TO 5mm:±0.1	ANGLES						
					ABOVE 5mm:±0.2	±1.5°	NO	DATE	REVISIONS		BY	APPD
4	COVER	LCP	1		TITLE: CONNECTOR			UNIT : MM	ROHS	DWN		
3	CONTACT FOOT	BRASS	XX	SN-PLATED	PART NO.: PH2001-LT-XX			SCALE: 2:1	COMPLIANT	CHK'D		
2	CONTACT	BRASS	2	SN-PLATED	HAUYU(HONGKONG)LIMITED 皓宇(香 港)有限公司					APPD		
1	HOUSING	LCP	1					PRO.AGL:		REV :A0		
NO.	PART	NAME	MATERIAL	QTY	FINISHING							