



印制线路板

Circuits	Dimensions (mm)			Circuits	Dimensions (mm)		
	A	B	C		A	B	C
2.5LT-2P	2.5	7.50	6.0	2.5LT-12P	27.5	32.5	31.0
2.5LT-3P	5.0	10.0	8.5	2.5LT-13P	30.0	35.0	33.5
2.5LT-4P	7.5	12.5	11.0	2.5LT-14P	32.5	37.5	36.0
2.5LT-5P	10.0	15.0	13.5	2.5LT-15P	35.0	40.0	38.5
2.5LT-6P	12.5	17.5	16.0	2.5LT-16P	37.5	42.5	41.0
2.5LT-7P	15.0	20.0	18.5	2.5LT-17P	40.0	45.0	43.5
2.5LT-8P	17.5	22.5	21.0	2.5LT-18P	42.5	47.5	46.0
2.5LT-9P	20.0	25.0	23.5	2.5LT-19P	45.0	50.0	48.5
2.5LT-10P	22.5	27.5	26.0	2.5LT-20P	47.5	52.5	51.0
2.5LT-11P	25.0	30.0	28.5				

					TOLERANCE UNLESS SPECIFIED							
					UP TO 5mm: ±0.1	ANGULAR						
					ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD
3	TERMINAL	BRASS	XX	Sn-PLATED	TITLE: XH 2.5mm connector			UNIT : MM	ROHS COMPLIANT	DWN	WM	
2	CONTACT	BRASS	2	Sn-PLATED	MODEL: XH2500-LT-xx			SCALE: 1:1		CHK'D	GYW	
1	CASE	LCP(UL94V-0)	1	BEIGE	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司					APPD	WRB	
NO.	PART NAME	MATERIAL	QTY	FINISHING				PRO.AGL:		REV :A0		