





环保物料

TEL:0769-82001899



P. C. B LAYOUT

Technical Data

Material:

Pin(outer sleeve):Brass,machined CuZn38Pb2

Plating(outer sleeve):

Tin Plated:2 μ m/80 μ "Ni, 5 μ m/200 μ "Sn

Gold Plated:2 μ m"/80 μ "Ni, 0.8 μ " gold

Insuiator:PPS UL94V-0

Electrical:

Current rating:3Amps/contact max.

Contact resistance: $\leq 4m\Omega$ /contact

Insuiation resistance: $\geq 1000M\Omega$ at V=100V

Operaing voitage:60VAC/DC

Mechanical:

Operaling temperature:-40 $^{\circ}$ C to+105 $^{\circ}$ C

Soldering temperature:+255 $^{\circ}$ C

Critical Dimensions:⊛

TOLERANCE UNLESS OTHERWISE

X.	± 0.30	X $^{\circ}$	$\pm 5^{\circ}$
.X	± 0.20	.X $^{\circ}$	$\pm 2^{\circ}$
.XX	± 0.08	.XX $^{\circ}$	$\pm 1^{\circ}$
.XXX	± 0.03	.XXX $^{\circ}$	$\pm 0.5^{\circ}$

DRAWN

CK tan

CHKD

APPD

VIEW



XFCN 兴飞连接器有限公司
XFCN CONNECTORS CO.,LTD.

PRODUCT NAME 2.54mm IC Socket Connectors

PART. NO. IC254V-12-10-1000A

SHEET 1/1

DATE 2020.04.12

UNITS mm

SCALE 1:1

DWG NO. 009

AO

VER

MODIFICATION

DRAW

DATE

1 2 3 4 5 6 7 8 9 10