	1 2 3 环保物料 3	3	4	5	6	1 7	8	9 TEL:07	10 769-82001899	7
A										A
						cations Rating: 2Amp	0.10		lo.of Dimension	
В					Insulat Dielect Contact	tion Resistanc cric Withstadi c Resistace: 2	e: 1000MΩ MIN. ng: 500V AC	°C	/Row A B 02 2.0 4.6 03 4.0 6.6 04 6.0 8.6 05 8.0 10.6 06 10.0 12.6	В
C	1 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	<u>+</u> , <u>+</u>		$ \begin{array}{c} $	Materia Post: H	al Brass Tin/Plat Gold/Tin Over	Nickel	seconds)	$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	
D					Bass: N	√ylon6T UL 94V	7-0		$\begin{array}{cccccccccccccccccccccccccccccccccccc$	D
E	0.5*0.2 2.0±0.05 2.0*No.of Contacts-2.0=A±0.25		2.8±0.2						23 44.0 46.6 24 46.0 48.6 25 48.0 50.6 26 50.0 52.6 27 52.0 54.6 28 54.0 56.6	E
_			<u>~</u>]						29 56.0 58.6 30 58.0 60.6 31 60.0 62.6 32 62.0 64.6 33 64.0 66.6 34 66.0 68.6	
F _									35 68.0 70.6 36 70.0 72.6 37 72.0 74.6 38 74.0 76.6 39 76.0 78.6 40 78.0 80.6	
G			TOLERANCE UNL X. ± 0.30		DRAWN CK ta CHKD		■ N XFCN CONNEC	有限公司	SHEEI 1/1 DATE 2020.04.1	$\frac{1}{2}$ G
	AO		$\begin{array}{c} . X \pm 0.20 \\ . XX \pm 0.08 \end{array}$	$X^{\circ} \pm 2^{\circ}$ $XX^{\circ} \pm 1^{\circ}$	APPD	PRODUCT NAME	2.00mm Female He		UNITED mm	
	VER MODIFICATION 1 2 3	DRAW DATE	4. XXX ±0.03	$\frac{1}{5}$	$\frac{\text{VIEW}}{6} \in$	\exists PART. NO. 7	PM200V-11- 8	xx-H43	DWG NO. 009	