



PCB LAYOUT



Material

Insulator: Glass filled PBT, (UL 94V-0)

Contact : Brass

Electrical Characteristics

Current rating: 2AMP

Dielectric Withstanding Voltage: AC 500V for 1 Minute.

Insulator Resistance: 1000MΩ Min. AT DC 500V.

Contact Resistance: 20mΩ Max.

Operating Temperature: -45°C ~ +105°C

PIN	尺寸	A±0.15	B±0.2	C±0.2	D±0.1
DR-9P		17.90	25.00	30.80	12.50
DR-15P		26.50	33.30	39.20	12.50
DR-25P		40.00	47.10	53.05	12.50
DR-37P		56.50	63.50	69.44	12.50

		Solder Type D-sub Lock screw		上海洲日电子有限公司	
		DR-9P/15P/25P/37P		Shanghai Zhouri Electronics CO.,LTD	
		Male		上海康司玛电子设备进出口有限公司	
X.	±0.3	±5°		Shanghai KangSiMa Eletronic Equipment	
X.X	±0.2	±3°		import and export Co.,LTD	
X.XX	±0.15		20171018 A/0	TEL:86-21-34975176/51571121	
			20171018	ZR20171018-DR-102	
			20171018	物料编号	1:1 mm 图幅 A4
			20171018		: 1 1

