

MATERIAL:

Cover:Nylon66,UL rated:94V-2 min

Base:Nylon66,UL rated:94V-2 min

Terminal:Brass,silver or tin plated

Rating: 10A 125V AC (UL CUL)

6A 250V AC (UL CUL VDE CE CQC)

Function:ON-OFF

Contact Resistance: 50mΩ Max

Insulation Resistance: DC 500V 100MΩ Min


Dielectric Strength: AC1500V 1 minute

Electrical life: 10,000 cycles


Operating Temperature: 0°C~85°C

Safety Approval:

CUT-OUT



	X	Y
0.75~1.25	19.2-0.1	113.0+0.1
1.25~2.00	19.4-0.1	113.0+0.1
2.00~3.00	19.8-0.1	113.0+0.1



				公差 TOLERANCES				角度 ANGLE ±1°		单位 DIMENSION UNIT mm.					
		版本 VERSION		A0		比例尺 SCALE		1:1		日期 DATE		品名 TITLE		图号 DRAWING NO	
		核准				核对				绘图		MR-2-120-C5L-BG-12V		MR-2-120-C5L-BG-12V_A0	
版本 VER.	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	APPROVED BY	CHECKED BY	DRAWN BY	孙成								