

MATERIAL:

Cover:Nylon66, UL rated:94V-2 min
 Base:Nylon66, UL rated:94V-2 min
 Terminal:Brass, silver or tin plated
 Rating:6A 125V AC (UL CUL)
 3A 250V AC (UL CUL VDE CE CQC)

Function:ON-OFF

Contact Resistance:50mΩ Max

Insulation Resistance:100MΩ Min

Dielectric Strength:2000VAC 1 minute


Dielectrical life:10,000 cycles

Mechanical life:50,000 cycles


Operating Temperature:-20℃~80℃

Safety Approval:     

CUT-OUT



	X	Y
0.75~1.25	13.6-0.18.7±0.1	
1.25~2.00	13.7-0.18.7±0.1	
2.00~3.00	13.8-0.18.7±0.1	



公差 TOLERANCES .X±0.3 .XX±0.15 角度 ANGLE ±1° 单位 DIMENSION UNIT mm.

版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	核准 APPROVED BY	核对 CHECKED BY	绘图 DRAWN BY	品名 TITLE	图号 DRAWING NO
						孙成	MR5-130-C3N-BB	1040040