



PCB LAYOUT

Function:(ON)-OFF
 Rating: 0.5A 30VDC
 0.25A 50VDC
 Contact Resistance: 50mΩ MAX.
 Insulation Resistance: 100MΩ min.at 500VDC
 Dielectric Strength: 1000 VAC rms.
 Electrical life: 50,000 cycles
 Mechina life: 100,000 cycles
 Operating Temperature: -20°C~65°C
 Relative Air Humidity:45%~85%
 Operating Pressure:400±100gf
 Operating Stroke:1.4±0.3mm

MATERIAL:

Button:ABS,UL rated:94V-2 min
 Base:PBT,UL rated:94V-2 min
 Terminal:Brass,silver or tin plated



				公差 TOLERANCES				.X± 0.5 .XX± 0.3		角度 ANGLE ±1°		单位 DIMENSION UNIT mm.	
				版本 VERSION		A0		比例尺 SCALE		1:1		日期 DATE	
				核准				核对				品名 TITLE	
版本 VER				变更说明 CHANGE DESCRIPTION				日期 DATE		ECN NO.		图号 DRAWING NO	
				APPROVED BY				CHECKED BY				DRAWN BY 孙成	
										2021.09.08		PB16-ABN-S3	
												1080001	