



- 备注：
 1.外壳镗雕D-SWITCH和PBM (代码A3)；
 2.拧螺母，配垫圈。

Nut Torque:5~14Nm
 Protection Grade:IP67,IK08
 Base:PA66
 Shell:Aluminum alloy anodizing black
 Button:PC
 Lamp Type:LED
 Forward current:20mA
 Lamp Life:50000H
 Insulation Resistance:100MΩ MIN.
 Dielectric Strength: 1500VAC 1 minute
 Operating Temperature:-20°C~80°C
 Relative Air Humidity:45%~85%
 Safety Approval:



| | | | | | | | |
|---------------|--------|---------|----------|-----|----|----------------|-----|
| 公差 TOLERANCES | .X±0.5 | .XX±0.3 | 角度 ANGLE | ±1° | 单位 | DIMENSION UNIT | mm. |
|---------------|--------|---------|----------|-----|----|----------------|-----|



| | | | | | | | | | | | |
|--------|-------------------------|---------|---------|------------|----------------|-----------|---------------|------------|-------------|---------------------------------|---------------|
| 版本 VER | 变更说明 CHANGE DESCRIPTION | 日期 DATE | ECN NO. | 版本 VERSION | 核准 APPROVED BY | 比例尺 SCALE | 核对 CHECKED BY | 日期 DATE | 绘图 DRAWN BY | 品名 TITLE | 图号 DRAWING NO |
| | | | | A0 | | 1:1 | | 2022.03.07 | 孙成 | PBM-30111-FV-V4-A24-A6S-A3-0004 | 1030462 |