



备注：
1.外壳镗雕D-SWITCH和PBM (代码A3)；
2.拧螺母，配垫圈。

Nut Torque:5~14Nm
Protection Grade:IP67,IK08
Base:PA66
Shell:Aluminum alloy anodizing black
Button:PC
Lamp Type:LED
Forward current:20mA
Lamp Life:50000H
Insulation Resistance:100MΩ MIN.
Dielectric Strength: 1500VAC 1 minute
Operating Temperature:-20°C~80°C
Relative Air Humidity:45%~85%
Safety Approval:

公差 TOLERANCES .X±0.5 .XX±0.3 角度 ANGLE ±1° 单位 DIMENSION UNIT mm.



版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	版本 VERSION	核准 APPROVED BY	比例尺 SCALE	核对 CHECKED BY	日期 DATE	绘图 DRAWN BY	品名 TITLE	图号 DRAWING NO
				A0		1:1		2022.03.07	孙成	PBM-30111-HV-V4-A24+A6S-A3-0004	1030464