



备注：
1. 外壳镗雕D-SWITCH和PBM (代码A3) ；
2. 拧螺母，配垫圈。

Nut Torque:5~14Nm
Operating Pressure:700gf ±200gf
Operating Stroke:2.6mm±0.5
Protection Grade:IP67,IK08
Function:(ON)-OFF
Contact:Silver Alloy
Base:PA66
Shell:Aluminum alloy anodizing black
Button:PC
Lamp Type:LED
Forward current:20mA
Lamp Life:50000H
Rating (Resistive load):5A 250V (AC)
Contact Resistance:50mΩ MAX.
Insulation Resistance:100MΩ MIN.
Dielectric Strength:1500VAC 1 minute
Electrical life:50,000 cycles
Mechanical life:100,000 cycles
Operating Temperature:-20°C~80°C
Relative Air Humidity:45%~85%
Safety Approval:

CUT-OUT

公差 TOLERANCES .X±0.5 .XX±0.3 角度 ANGLE ±1° 单位 DIMENSION UNIT mm.



版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	版本 VERSION	比例尺 SCALE	日期 DATE	品名 TITLE	图号 DRAWING NO
				A0	1:1	2022.03.07	PBM-30M12-HR-R4-A24-A6S-A3-0004	1013284
				核准 APPROVED BY	核对 CHECKED BY	绘图 DRAWN BY		
						孙成		