


	X	Y
0.75~1.25	30.0+0.1	122.0+0.1
1.25~2.00	30.2+0.1	122.0+0.1
2.00~3.00	30.4+0.1	122.0+0.1



MATERIAL:

Body:Nylon66, UL rated:94V-2 min

Actuator:Nylon66, UL rated:94V-2 min

Terminal:Brass,silver or tin plated

Rating: 40A 125V AC

25A 250V AC

Function:ON-OFF

Contact Resistance: 50mΩ Max

Insulation Resistance: DC 500V 100MΩ Min

Dielectric Strength: 2000VAC 1Am of 1 minute

Dielectrical life: 10,000 cycles

Mechanical life :50,000 cycles

Operating Temperature: -20℃~80℃

Safety Approval:



D-SWITCH
东莞市德致电子有限公司
D-SWITCH ELECTRONICS CO.,LTD.

公差 TOLERANCES .X±0.3 .XX±0.15 角度 ANGLE ±1° 单位 DIMENSION UNIT mm.

版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	核准 APPROVED BY	核对 CHECKED BY	绘图 DRAWN BY	品名 TITLE	图号 DRAWING NO
							R-6-210-C5L-BG-220V	1040134