



尺寸	X	Y
0.75~1.25	19.2-0.1	13.0+0.1
1.25~2.00	19.4-0.1	13.0+0.1
2.00~3.00	19.8-0.1	13.0+0.1

MATERIAL:

Cover: Nylon66, UL rated: 94V-2 min
 Base: Nylon66, UL rated: 94V-2 min
 Terminal: Brass, silver or tin plated
 Rating: 10A 125V AC (UL CUL)
 6A 250V AC (UL CUL VDE CE CQC)
 Function: ON-OFF
 Contact Resistance: 50mΩ Max
 Insulation Resistance: DC 500V 100MΩ Min
 Dielectric Strength: AC3000V 1 minute
 Electrical life: 10,000 cycles
 Operating Temperature: 0°C~85°C
 Safety Approval:

CUT-OUT

公差 TOLERANCES .XX±0.5 .XX±0.3 角度 ANGLE ±1° 单位 DIMENSION UNIT mm.



版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	核准 APPROVED BY	核对 CHECKED BY	绘图 DRAWN BY	品名 TITLE	图号 DRAWING NO
						孙成	MR-2-210-CSL-WU-220V	1040157