


CUT-OUT

	X
0.75~1.25	20.2
1.25~2.00	20.4
2.00~3.00	20.6



MATERIAL:
 Cover: Nylon66, UL rated:94V-2 min
 Base: Nylon66, UL rated:94V-2 min
 Terminal: Brass, silver or tin plated
 Rating: 10A 125V AC (UL CUL)
 6A 250V AC (UL CUL VDE CE CQC)
 Function: ON-OFF
 Contact Resistance: 50mΩ Max
 Insulation Resistance: DC 500V 100MΩ Min
 Dielectric Strength: AC1500V 1 minute
 Electrical life: 10,000 cycles
 Operating Temperature: 0°C~85°C
 Safety Approval:



公差 TOLERANCES .X± 0.5 .XX± 0.3 角度 ANGLE ±1° 单位 DIMENSION UNIT mm.

版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECON NO.	版本 VERSION	核准 APPROVED BY	比例尺 SCALE	核对 CHECKED BY	日期 DATE	绘图 DRAWN BY	品名 TITLE	图号 DRAWING NO
				A0		1:1		2021.11.05	孙成	MR-2-210-R5L-BG-220V	1040155