




PCB LAYOUT




Specifications:

- 规格:
 Voltage rating:50V AC/DC
 额定电压: 50V AC/DC
 Current rating:1A AC/DC
 额定电流: 1A AC/DC
 Contact Resistance:≤20MΩ
 接触电阻: ≤20MΩ
 Insulation Resistance:≥100MΩ
 绝缘电阻:≥100MΩ
 Dielectric strength:250V AC/minute
 耐压: 250V AC/minute
 Plug-in force: ≤3N(per pin)
 插入力: ≤3N (per pin)
 Plug-out force:≥0.3N (per pin)





SECTION A-A



X1254W V S-XX-LP SW
 ① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No
- ② Category:W-WAFER
- ③ Welding Board Angle:V-90°
- ④ Welding Way:S-SMT
- ⑤ Row No-Pin No:XX-02-07PIN
- ⑥ Material:LP-LCP 94V-0
- ⑦ Plating Category:SW-Matte Tin Plating(Tin:70u Min)

Circuits	Dinansin mm		Circuits	Dinansin mm	
	A	B		A	B
2	5.58	1.25	6	10.85	6.25
3	7.10	2.50	7	12.10	7.50
4	8.35	3.75			
5	9.60	5.00			



X1254WVS-XX-LPSW	PA9T UL 94V-0	Tin-Plated	Tin-Plated	X1254W
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

生效 日期

文件工程章








DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm/in	1.25mm Crimp Style Connectors
APPD		DATE		SIZE: A4	DWG NO.:
					X1254WVS-XX-LPSW
XKB INDUSTRIAL PRECISION CO.,LIMITED				WEIGHT	SHEET
				1/1	REVISION
					A0

REVISIONS

UNSPECIFIED TOLERANCES

DATE REVISED APPROVED

units: mm
 tolerance:
 X.X ±0.2mm
 X.XX ±0.1mm
 X.XXX ±0.05mm



Specifications:
 规格:
 Voltage rating:50V AC/DC
 额定电压: 50V AC/DC
 Current rating:1A AC/DC
 额定电流: 1A AC/DC
 Contact Resistance:≤20MΩ
 接触电阻: ≤20MΩ
 Insulation Resistance:≥100MΩ
 绝缘电阻: ≥100MΩ
 Dielectric strength:250V AC/minute
 耐压: 250V AC/minute
 Plug-in force: ≤3N (per pin)
 插入力: ≤3N (per pin)
 Plug-out force:≥0.3N (per pin)

X1254 WVS -XX-LP SW
 ① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No
- ② Category:W-WAFER
- ③ Welding Board Angle:V-90°
- ④ Welding Wway:S-SMT
- ⑤ Row No-Pin No:XX-02-07PIN
- ⑥ Material:LCP-LCP 94V-0
- ⑦ Plating Category:SW-Matte Tin Plating(Tin:70u Min)

Circuits	Dinansin mm		Circuits	Dinansin mm	
	A	B		A	B
8	13.35	8.75	12	18.35	13.75
9	14.60	10.00	13	19.6	15.00
10	15.85	11.25	14	20.85	16.25
11	17.10	12.50	15	22.10	17.50

X1254WVS-XX-LPSW	PA9T UL 94V-0	Tin-Plated	Tin-Plated	X1254W
	LCP UL 94V-0	Brass	Phosphor Brass	
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Terminal

DSND	DATE	SCALE: N/A	MODEL TYPE: Wire to board connector
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	2.54mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO.,LIMITED			X1254WVS-XX-LPSW
WEIGHT	SHEET	REVISION	
	1/1	A0	

广东星坤科技股份有限公司

生	日期
效	日期
MARK	DESCRIPTION
文件	工程章

REVISIONS

DATE REVISED APPROVED

UNSPECIFIED TOLERANCES

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn