



3D VIEW

Specifications:

规格:
 Current rating:5A AC/DC
 额定电流: 5A AC/DC
 Voltage rating:500V AC
 额定电压: 500V AC
 Withstanding voltage:500V AC/MIN
 耐受电压: ≥500V AC/分钟
 Temperature range:-25 °C-+105 °C
 温度范围: -55 °C-+105 °C
 Insulation resistance:1000MΩMIN
 绝缘电阻: ≥1000MΩ
 Contact resistance:30mΩMAN
 接触电阻:≤30mΩ
 Material And FINISHED:
 材料和成本:
 INSULATOR:PBT+30 % GF UL 94V-0
 绝缘体: pbt+30 % gf ul 94-0
 SHELL:STEEL, NI FINISHED
 外壳: 钢、聂加工
 CONTACT MATERIAL:BRASS SELEVITE GOLD FINISHED
 触点材料: 黄铜SELEVITE

X03 XX F X X X X

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series NO.
- ② Row No.Pin No.XX-09,15;25;37
- ③ Welding Board Angle :F-Fmale
- ④ T: Tradutional C: Car-pin
- ⑤ Planting Category: 1:1U 2:2U 3:3U 4:5U 5:15U 6:30U 7:AuSn
- ⑥ B:BLACK W:White BL:Blue Y:Yellow G:Green R:Red
- ⑦ 1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4; 5:TYPE-5; 6:TYPE-6

NO. OF CONTACT	A	B	C
09	30.80	24.99	16.35
15	39.20	33.30	24.75
25	53.05	47.04	38.35
37	69.40	63.50	54.75

铆合方式	TYPE-1: 铆合	TYPE-6: 直铆锁	TYPE-3: 叉锁	TYPE-2: 铆合锁螺丝
图式				

DSND		DATE		SCALE: N/A	MODEL TYPE:
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm/in	DWG NO.:
APPD		DATE		SIZE: A4	X03XXFXXXX
				XKB INDUSTRIAL PRECISION CO.,LIMITED	WEIGHT
					1.0g
					SHEET
					1/1
					REVISION
					A0

MARK	DESCRIPTION	DATE	REVISED	APPROVED	units: mm
ΔX					tolerance: X.X ±0.2mm
ΔX					X.XX ±0.1mm
ΔX					X.XXX ±0.05mm
					UNSPECIFIED TOLERANCES
REVISIONS					
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn					