





D1RFRD006

REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE
△		Drawing Revise	Haoyi	03/18/06
△		增加UL字样	CSX	12/14/06
△	12-0283	Drawing Revise	YHG	12/14/12
△	14-0344	增加CE 字样和技术参数修改	SHB	09/28/14




1.00±0.05



- 1Y
(Color) 1.(Grey)
2.(Blue)
3.(Black)
4.(Green)
5.(Orange)
6.(Red)
7.(Transparent)
8.(Yellow)
9.(White)

- NOTES:
1.DIMENSION SHALL BE INTERPRETED PER ASME Y14.5-2009
2.PITCH: 5.0MM ,POLES: 2P-24P
3.RATED VOLTAGE/CURRENT:UL 300V/10A IEC 250V/17.5A
4.OPERATION TEMPERATURES: -40℃~+105℃
5.WITHSTANDING VOLTAGE: AC2000V/1MIN
6.INSULATION RESISTANCE: 5000MΩ/DC1000V
7.WIRE RANGE: 14~26AWG,0.5~1.5MM²
8.MAX.TORQUE VALUE:M2.5,3.0KGF.CM
9.UNDIMENSIONED TOLERANCES:

PITCH RANGE IN MM		NOMINAL DIMENSION RANGE IN MM				
TO	OVER	TO	OVER	TO	OVER	
6	10	30	60	100		~
10	10	30	60	100	150	∇
10	24	30	60	100	150	∇



ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTES
4	DG126 "+" Screws-M2.5	S000001510(H)	XX	steel	Cr ²⁺ Zn
3	DG308 Spring	X000000160(H)	XX	spring steel	
2	DG308 Pin	4008800020(H)	XX	Brass	Tin plated
1	DG126-5.0-Housing	4018AYYXXA(H)	1	PA66	UL94V-0

<p>DETAILED LIST</p> <p>ANGLES ± 1°</p> <p>THIRD ANGLE PROJECTION</p>	<p>MATERIAL:</p> <p>FINISH:</p> <p>PART NO.:</p> <p>APPR: Jean rof/ky</p> <p>CHK: Apron 10/21/14</p> <p>DRFT: HADYH 04/05/05</p>	<p>NAME:</p> <p>DG126-5.0-XXP-1Y-00A(H)</p> <p>TITLE: ASSEMBLY DRAWING</p> <p>DRAWING NO.: DG126-5.0-E02</p> <p>DO NOT SCALE DRAWING</p>
---	--	--

<p>宁波高正电子有限公司</p> <p>DEGSON®</p> <p>DEGSON ELECTRONICS CO.,LTD</p>	<p>REV 14</p> <p>SHEET 1/1</p>
--	--------------------------------